



Core Alignment fusion splicer

T-57C+

Powered by





Power through with ease



Proven field toughness



High environmental Smart and ease resistance





Reduce work time Splicing 6s Heating 15s

Specifications				
Item		T-57C+		
Optical fibre requirements	Material	Silica glass		
	Fibre count / Profile types	Single / SMF(G.652), MMF(G.651), DSF(G.653), NZDSF(G.655), BIF(G.657)		
	Fibre diameter	Cladding diameter: 80 ~ 150µm, Coating diameter: 100 ~ 1,000µm		
	Cleave length	5 ~ 16mm with coating clamp		
	Splice loss (typical)*1	SMF: 0.02dB, MMF: 0.01dB, DSF: 0.04dB, NZDSF: 0.04dB, BIF: 0.02dB		
	Return loss (typical)	60dB or greater		
	Splice time (typical)	6sec(SM G652 Quick Mode), 8sec(Auto Mode)		
Cham danid	Heating time (typical)	15sec (FPS-61-2.6 sleeve, S60mm 0.25)		
Standard	Splice & Heat cycles per battery full charge*2	Approx. 310 (BU-16)		
performance	Fibre view & magnification	2 CMOS cameras observation, 350X (zoom: 700X) for X or Y single axis view. 270X for both X & Y dual axis view		
	Proof test	1.96 ~ 2.09N		
	Applicable protection sleeve	60mm, 40mm & Sumitomo Nano sleeves		
D	Splice programs	Max. 300, 40 are pre-optimised, 260 editable by user		
Programs	Heating programs	Max. 100, 23 are pre-optimised, 77 editable by user		
	Splice image capture / Splice data storage	200 images / 10,000 splice data (internal memory only) 50,200/20,000 (with 16GB SD card)		
	Multi clamps	Provided, 250 m, 900 m tight & loose buffer fiber, 2&3mm jacket cord and rectangular drop cable, 3.5mm round drop cable		
- ··	Reversible coating clamps	Provided		
Functions	Onboard user training video	Provided		
	Automatic fibre identification	SMF / MMF / DSF / NZDSF / BIF / Other		
	Automatic arc calibration	Automatically compensates for environmental condition changes		
	Display of remaining Splice & Heat cycles	Provided (Battery mode)		
	Size	128(W) x 154(D) x 130(H) mm (without anti-shock rubber)		
Size / Weight	Weight	1.7kg (without Battery) / 2.1kg (with Battery BU-16)		
	Monitor	5.0" touch screen color LCD display		
	DC output	DC 12V (for JR-6+)		
Terminals	USB port	USB 2.0 (mini-B type)		
	Storage media	SD / SDHC memory card MAX32GB		
Power supply	AC input	AC 100 ~ 240V, 50/60Hz (ADC-16)		
	DC input	DC 10 ~ 15V		
	Battery pack	Li-ion 10.8V, 6,400mAh (BU-16)		
Operating condition		Altitude : $0 \sim 6,000$ m, Temperature : - $10 \sim +50$ °C, Humidity : $0 \sim 95$ % (non-condensing), Wind velocity : up to 15 m/sec		
Storage condition		Temperature: -40 ~ +80°C, Humidity: 0 ~ 95% (non-condensing), Battery: -20 ~ +30°C (long term)		
Electrode life *3		6,000 arc discharges		
Software updates		Internet		
Data management		Can be stored, edited and analyzed by dedicated PC software		

- 1: Average value of the final inspection in room temperature with Sumitomo identical fibre. Measured by cut-back method relevant to ITU-T and IEC standards.
- Average value of the final inspection in contemporary and the operating environment.
 S. Splice & Heat cycles may vary depending on the battery status and the operating environment.
 3. Achieved in lab condition. Electrode life may vary depending on the operating environment.

Environmental Durability*				
	Test details			
Shock resistance	Drop from 76cm on 5 faces(excluding top face), 4 edges and corners(bottom face only)			
Impact resistance	Equivalent to IK07 on LCD monitor			
Water resistance	Equivalent to IPx2			
Dust resistance	Equivalent to IP5x			

* Splicer operation after shock, impact, water or dust tests, was confirmed under battery power, by Sumitomo.

Does not guarantee the product will not be damaged by these conditions.

Basic Accessories Part name Part No Qty. AC adapter ADC-16 1 pc AC power cord PC-AC<X>* 1 pc Cooling tray 1 pc Spare electrode ER-10 1 pair Quick reference guide 1 pc Carrying case with worktable CC-72 1 pc Hand strap 1 pc USB cable 1 pc

X=2(USA), 3(EU), 5(UK/HK), 6(AUS), 7(SOUTH AFRICA)
Items listed in the table are typical contents included with the splicer body. Overall kit content may vary regionally. Please check with your local authorised reseller to confirm kit content in your region.

Accessories						
	Part name	Part No.	Remarks			
Accessories for Splicer	Fibre holder	FHS-025	For Φ0.25mm single fibre			
		FHS-09	For Φ0.9mm single fibre			
		FHS-025/LB5	For 0.9mm loose buffered single fibre			
		FHD-1	For indoor / outdoor rectangular drop cable			
		1SM-ST	For indoor rectangular drop cable			
		FHC-3	For 3mm cable			
		Lynx2-UML-S	For Φ3mm cord and Φ 0.9mm single fibre			
	Battery pack	BU-16	Li-ion 6,400mAh			
	Battery charger	BC-16	_			
	Car battery cable	PCV-16	Vehicle 12V outlet			
	Electrode	ER-10	_			
Accessories	Handheld cleaver	FC-8R-FC	Automatic blade rotation cleaver with counter			
		FC-8R-F	Automatic blade rotation cleaver (no counter)			
	Bench-top Cleaver	FC-6R+	Auto blade rotation			
		FC-6S+	Single fibre cleaver			
	Jacket remover	JR-M03	Jacket remover for single fibre			
	Loose tube cutter	LTC-01	_			
	Alcohol dispenser	HR-3	_			
	Fibre protection	FPS-1	60mm, diameter after shrink approx. Φ3.2mm			
	sleeve	FPS-40	40mm, diameter after shrink approx. Φ3.2mm			
		FPS-61-2.6	61mm, diameter after shrink approx. Φ2.6mm			



Carrying case with worktable



Handy cleaver FC-8R series



Bench-top cleaver FC-6+ series



Jacket remover JR-M03



Available for Lynx-Custom Fit™ **Splice-On Connector**



Electrode ER-10

Sumitomo Electric Industries,